

Jewel®



"If any part of the loop should open (become disconnected or have out of limit resistance), the circuit will go into the alarm state" [ref TR20.20], nonetheless, due to the redundancy inherent in the dual wire wrist strap design, the operator will continue to be grounded via the second intact wire.

Per ESD Handbook TR20.20 section 5.3.9.2.2 Dual Conductor Resistance Continuous Monitors, "This type of monitor is used with a two wire (dual conductor) wrist strap. The wrist strap assembly consists of a two-wire ground cord and a wristband that has two isolated halves. When a person is wearing the wrist strap properly, the monitor measures the loop resistance consisting of one wire of the ground cord, one-half of the wristband, the person's skin, the second half of the wristband, and a second wire in the ground cord. If any part of the loop should open (become disconnected or have out of limit resistance), the circuit will go into the alarm state.

ESD Handbook TR 20.20 paragraph 5.3.2.4.4 Test Frequency "Because wrist straps have a finite life, it is important to develop a test frequency that will guarantee integrity of the system. Typical test programs recommend that wrist straps that are used daily should be tested daily. However, if the products that are being produced are of such value that knowledge of a continuous, reliable ground is needed, and then continuous monitoring should be considered or even required"

Continuous Monitors pay for themselves improving quality, productivity, eliminating wrist strap daily testing and test result logging. Per ESD-S1.1 paragraph 6.1.3 Frequency of Functional Testing "Daily [Wrist Strap] testing may be omitted if constant monitoring is used."

Improve wrist strap contact with Reztore™ ESD Hand Lotion

*U.S. Patents 6,052,053 and 6,205,408

Dual Wire Coil Cord provides redundancy; even if one conductor is severed, operator has reliable path-to-ground with other wire.



- Used with resistive loop technology continuous monitor, continuously verifies the proper resistance to ground of the operator
- Coil cord with molded 1 Megohm current limiting resistor on both ground paths to protect user from shock due to inadvertent contact with line voltage
- Superior strain relief design, dual conductor cord utilizes single wire extrusion to significantly increase flexlife. Flex life average >9,000,000 cycles (per ESD S1.1 Bending Life Test, greatly exceeding the 16,000 average cycle requirement). Break load average 30 pounds.
- Dual T-3067 tinsel conductor. Consisting of stranded polyester wrapped in copper. High flex life. Equivalent to 29 gauge (cir mil and/or ohms)
- 3.5mm phono plug connector
- Single snap head allows operators to quickly and easily attach and detach the cord from the wristband (Use Vermason wristband)
- Custom manufactured right angle mono-plug reduces chance of accidental disconnects providing more secure ground connection
- Patented* dual wire technology
- Superior warranty - See details of 1 year Limited Warranty at <http://www.vermason.co.uk/LimitedJewelWarranty.aspx>
- UL listed

Use patented* Dual Wire Wrist Strap with Vermason Dual Wire Continuous Monitor

Item	Description
229943	1.8M Coil Cord, 4mm female snaps, right angle mono plug
229944	3.65M Coil Cord, 4mm female snaps, right angle mono plug
229945	6.1M Coil Cord, 4mm female snaps, right angle mono plug

Thermoplastic elastomer strain relief molded on. Flex life average >9,000,000 cycles (per ESD S1.1 Bending Life Test, greatly exceeding the 16,000 average cycle requirement). Break load average 30 pounds.

Unless otherwise noted, tolerance ± 10%

Specifications and procedures subject to change without notice.



Made in America

Vermason

JEWEL® COIL CORD, DUAL-WIRE, ONYX, RIGHT ANGLE MONO PLUG

VERMASON
UNIT C, 4TH DIMENSION, FOURTH AVENUE, LETCHWORTH,
HERTS, SG6 2TD UK
PHONE: +44 (0) 1462-672005, FAX: +44 (0) 1462-670440
E-MAIL: Service@Vermason.co.uk, INTERNET: Vermason.co.uk

Drawing Number
229943

DATE:
March
2011