



Description

- Dissipative Yellow Bottle with swan neck spout
- Promotes ESD control awareness
- Used to hold water for wetting sponges at soldering stations, to hold cleaning agents or similar liquids
- Simply squeeze the bottle to release some contents through the spout.
- No Migratory Additives - reduces the chance for contamination from the bottle
- LDPE durAstatic bottles are dissipative; electrostatic charges are removed to ground when handled by a grounded operator or in contact with ESD worksurface
- Highly visible with ESD protective symbol, allowing people to immediately know the bottle is ESD protective
- Available in 240mL or 480mL Bottle

Specifications

Bottle volume resistance 1×10^4 to $< 1 \times 10^{11}$ ohms per IEC 61340-2-3
 Meets ANSI/ESD S20.20, EN 61340-5-1, ANSI/ESD S541 and EN 61340-5-3



239900



239915

239900

- Material = LDPE
- Size = 240mL
- Base Diameter = 57mm
- Neck Size = 28-400
- Height = 197mm

239915

- Material = LDPE
- Size = 480mL
- Base Diameter = 74mm
- Neck Size = 28-400
- Height = 228mm

<u>239900</u>	240mL Bottle, Dissipative LPDE, Yellow, Pack of 5
<u>239915</u>	480mL Bottle, Dissipative LPDE, Yellow, Pack of 5

"It should be understood that any object, item, material or person could be a source of static electricity in the work environment. Removal of unnecessary nonconductors, replacing nonconductive materials with dissipative or conductive materials and grounding all conductors are the principle methods of controlling static electricity in the workplace, regardless of the activity." [ESD Handbook ESD TR20.20 section 2.4 Sources of Static Electricity]

If not otherwise noted, tolerances ± 10%
 Specifications and procedures subject to change without notice.

durAstatic Dissipative Wash Bottles



VERMASON
 UNIT C, 4TH DIMENSION, FOURTH AVENUE, LETCHWORTH,
 HERTS, SG6 2TD UK
 PHONE: +44 (0) 1462-672005, FAX: +44 (0) 1462-670440
 E-MAIL: Service@Vermason.co.uk, INTERNET: Vermason.co.uk

Drawing Number
239900

DATE:
 May 2016