



- Handling gloves are worn to protect the operator's hands . In an ESD protected area the gloves should be conductive or static dissipative.
- Knitted fabric with 5mm stripe
- Surface resistance between 10E5 - 10E9 tested per IEC 61340-2-3
- Decay time within 0.3 seconds tested per Test method B.2 per EN 61340-5-1-1998
- Composition: 93% polyester filament yarn with 7% carbon compound filament yarn
- The gloves are washable. Use mild soap solution only. Do not use bleach or other strong cleaners as it destroys conductivity. Check conductivity after each wash.
- Wearing gloves does not negate the need for wrist straps or other effective personnel grounding methods.

Item	Description
72610	ESD Handling Glove, with Coated Finger Tips, Small
72611	ESD Handling Glove, with Coated Finger Tips, Medium
72612	ESD Handling Glove, with Coated Finger Tips, Large
72613	ESD Handling Glove, with Coated Finger Tips, XLarge

EN 61340-5-1 paragraph 5.2.6 Gloves and finger cots: "Gloves and finger cots made from electrostatic conductive or electrostatic dissipative material are essential if hand tools are used. Gloves and finger cots made from low charging material are permitted only in circumstances when hand tools are not used. Where gloves and finger cots are removed in the EPA, they should not be placed in close proximity to ESDS."

Glove Laundering

For proper operation, the ESD Gloves must be laundered periodically. Woolite works well. Liquid detergents are better than dry in that there is less caking and frictional wear. Launder glove in cool or warm water, tumble dry with low heat or hang dry. Machine washing works well if using a standard house machine on gentle cycle. It is not recommended to launder these gloves in heavy industrial laundry machines as it will lead to premature wear. Gloves should be tumbled dry using low heat. DO NOT BLEACH.



Made in Britain

Unless otherwise specified tolerance $\pm 10\%$

Specifications and procedures subject to change without notice.



ESD Handling Glove, with Coated Finger

CHARLESWATER LTD.
 UNIT 17. MILLBROOK BUSINESS PARK, SYBRON WAY
 CROWBOROUGH, EAST SUSSEX TN6 3JZ UNITED KINGDOM
 PHONE: 00 44 (0) 1892-665313, FAX: 00 44 (0) 1892-668838
 INTERNET: Charleswater.co.uk

Drawing Number
 72610.E

DATE:
 August
 2010