

A Donaldson Company

A WORLD LEADER IN FUME **EXTRACTION TECHNOLOGY**



ELECTRONICS, PHARMACEUTICAL & MEDICAL





The complete solution for fume cabinet extraction for various applications.

Partial enclosures are steadily becoming the preferred option for operator protection from fumes generated from processes such as hand soldering, solvent use, and other processes that produce harmful fumes.

This cabinet has been designed to work with the V 600 extraction system.

Technology



ProTECT service plan



SureCHECK quality standard

Key features of the FumeCAB 600

FumeCAB 600 Standard

Strong rigid construction Standard

V 600 filtration unit Optional

Powder coated white Standard

2 x 1.5 meters of 75mm flexible hose Standard

Technical specification

Contact BOFA at https://bofainternational.com/en/contact/

https://bofainternational.com/us/portal/datasheets/fumecab-600/
















Airflow through filters





Technical data			
	EU	US	
Dimensions (HxWxD)	355 x 610 x 420mm	13.98 x 24.02 x 16.54"	
Opening dimensions (HxW)	315 x 540mm	12.4 x 21.3"	
Recommended face velocity	0.5m/s	150f/min	

Technical data - V 600 extraction system		
	EU	US
Dimensions (HxWxD)	590 x 375 x 460mm	23.22 x 14.76 x 18.11"
Cabinet construction	Powder coated mild steel	Powder coated mild steel
Airflow / Pressure	350m³/hr / 96mbar	206cfm / 96mbar

Technical data - V 600 extraction system			
Electrical data	90-257v 1ph 50/60Hz Full load current: 12.5 amps / 1.1kw	90-257v 1ph 50/60Hz Full load current: 12.5 amps / 1.1kw	
Noise level	< 60dBA (at typical operating speed)	< 60dBA (at typical operating speed)	
Weight	35kgs	77lbs	
Approvals	CE	CE	

V 600 DeepPleat pre-filter specifications	
Filter media	Borosilicate
Filter media construction	Pleated
Filter efficiency	F8 (95% @ 0.9 microns)
Surface media area	6m² approx (64.56 ft²)

V 600 combined filter specifications		
HEPA filter media	Borosilicate	
HEPA media construction	Pleated with glue bead spacers	
Gas filter	Treated activated carbon	
Filter housing	Zintec mild steel	
Treated activated carbon	7.5kgs (16.5 lbs)	
Filter efficiency	99.997% @ 0.3 microns	

Part numbers		
Model	Part no.	Optional VOC monitoring
FumeCAB 600	A1020128	N/A
FumeCAB 600 and V600 fitted with combined HEPA/Gas filter	E1142A0005	A2003

Other languages

FumeCAB 600 French FumeCAB 600 <u>Italian</u>

Datasheet correct at time of publishing.

Where applicable, the carbon used in BOFA units is capable of removing a wide range of VOC's, however it is the responsibility of the user to ensure the carbon is suitable for their application. For specific applications, please contact us for details.

Think before you print! Please consider the environment before printing this document.

